



**EXPERTISE.**  
**PRODUCTS. SERVICES.**

Tube systems and installation solutions for reliable processes  
in the semiconductor, pharmaceutical, analytical and fine chemistry industries.

# “PROCESS RELIABILITY

is our motivation – for processes in the semiconductor, pharmaceutical and biotechnology industries. ”



## We connect processes with the highest purity

Dockweiler is a leading international manufacturer of stainless steel tube systems. The core business is the development of installation solutions for handling fluid and gaseous media in the semiconductor, pharmaceutical analytical and fine chemistry industries.

### **Our manufacturing expertise is your advantage**

Thanks to our manufacturing expertise, we find solutions which are economical and offer high process reliability. Consultancy and services are key components for us because our customers see us as an engineering partner.

Our specialists have extensive knowledge about all specifications and consult competently on choosing the right products. Our engineers plan and develop tailor-made components with you and see it through to implementation.

### **Cutting-edge products for processes with the highest purity**

Dockweiler supplies standard products such as tubes and fittings for highly technical sectors. We also offer tailor-made installation solutions, which fulfill the highest requirements for purity and precision. With inventory holdings of more than 1500 Kilometers in pipes and approximately 1 million fittings, we guarantee speedy availability.



### **Customer service from the very start**

The demands on industrial processes have increased steadily in recent years. The most important indicator of our performance is successful collaboration with our customers. Our service begins right at the planning stage: In addition to our product range, Dockweiler has continually developed its service features.

#### **Dockweiler Expertise**

<a href="#">Surface treatment</a>	Page 05
<a href="#">Welding Technology</a>	Page 06
<a href="#">Collaring</a>	Page 06
<a href="#">3D Bending</a>	Page 07
<a href="#">Cleanroom Production</a>	Page 07

#### **Dockweiler Products**

<a href="#">Tubes and Fittings</a>	Page 09
<a href="#">COAX Double-Wall Tube System</a>	Page 09
<a href="#">Presslok</a>	Page 09
<a href="#">Connection Components</a>	Page 10
<a href="#">Custom Fittings</a>	Page 10
<a href="#">Connections and Gaskets</a>	Page 11
<a href="#">Flexible Hoses</a>	Page 12
<a href="#">Ball Valves and Valves</a>	Page 13
<a href="#">Customized Solutions</a>	Page 14
<a href="#">Process Vessels</a>	Page 14
<a href="#">Welding Equipment</a>	Page 15

#### **Dockweiler Services**

<a href="#">Laboratory Services</a>	Page 17
<a href="#">Material Consulting</a>	Page 17
<a href="#">Cleaning Processes</a>	Page 17
<a href="#">Engineering Services</a>	Page 18
<a href="#">Training</a>	Page 18
<a href="#">Technical Documentation</a>	Page 18
<a href="#">Logistics and Warehouse Service</a>	Page 19
<a href="#">Certificates</a>	Page 20
<a href="#">Addresses Worldwide</a>	Page 22




We develop products for the highest standards – we set standards with our surface treatment. ”



### Treatment of inner surfaces for high purity

## Benefits of Surface Treatment

- optimal inner surfaces for high purity processes
- increased resistance to corrosion
- improved cleanability of the system
- reduced adhesion of particles due to extremely smooth surfaces



**ELECTROPOLISHED INNER SURFACE –** ▶  
Extremely smooth and pure with a surface quality  
of up to  $Ra \leq 0,13 \mu m$



## Qualities for Gases

The figure consists of two side-by-side charts showing the particle size distribution of various cleaning agents. The y-axis for both charts represents particle size in micrometers (µm), ranging from 0.1 to 1.0. The x-axis is unlabeled but represents a distribution metric.

**Left Chart (Liquid):**

- weldtron:** Indicated by a grey square, showing effectiveness for larger particles (up to 1.0 µm).
- bpe-direct:** Indicated by a red square, showing effectiveness for larger particles (up to 1.0 µm).
- safetron:** Indicated by a green square, showing effectiveness for smaller particles (down to 0.1 µm).

**Right Chart (Gas):**

- TCC \*\*\*:** Indicated by a teal square, showing effectiveness for larger particles (up to 1.0 µm).
- finetron:** Indicated by a blue square, showing effectiveness for larger particles (up to 1.0 µm).
- puretron:** Indicated by an orange square, showing effectiveness for larger particles (up to 1.0 µm).
- ultron:** Indicated by a yellow square, showing effectiveness for larger particles (up to 1.0 µm).
- weldtron:** Indicated by a grey square, showing effectiveness for smaller particles (down to 0.1 µm).

\* Hygiene grade in accordance with DIN 11864 / DIN 11865 / DIN 11866. \*\* in accordance with ASME BPE. \*\*\* not defined, Ra 0,80 µm on request





Collaring

Production know-how: how to

The collaring of T pieces, CIP lances or manifolds is well-developed Dockweiler know-how. **Closely-spaced outlets** often belong to the technical challenges faced. This is routine for our specialists. In combination with products resulting from our welding expertise, which stand out for their **particularly compact and flow-optimized construction**. Included in this are excentric outlets and outlets with various angles (for example, T-pieces with 45 degree outlets)

Benefits of Collaring Technology

- homogeneous transition contour from the main pipe to the branch pipe
- streamlined flow behavior
- effective welding preparation
- complete reduction in space for example in the production of manifolds
- compact component geometry

IO WELDING TECHNOLOGY FOR COMPLEX GEOMETRIES  
[Find out how that works here](#)



Welding Technology

Over 30 years' experience in cutting-edge technology

Dockweiler is a pioneer in the area of orbital welding. **With the 3D inside out welding technology (IO welding) we have developed new and exciting opportunities for innovative production capabilities.** In this way, closely-spaced outlets and those with lower dead space are produced in a highly-efficient manner. This 3D internal orbital welding technology is **ideal for complex geometries** and innovative components.



Benefits of Welding Technology

- 3D internal orbital welding technology for complex geometries such as 45° or 60° outlets and saddle welds
- precisely reproducible welding processes due to a parameter database and automatization
- consistent quality thanks to Dockweiler orbital welding with pressure and residual oxygen monitoring
- Minimization of  $\delta$  ferrite content
- low dead space and closely-spaced outlets
- machine-controlled TIG processes
- 100% weld seam testing
- straightforward documentation with computerized processes



Cleanroom Production

High purity environment for high purity products

For products which are used in the semiconductor industry, production must take place in a high purity environment. There must be no contamination from foreign particles or residues. These conditions are only possible in the cleanroom. High purity products such as manifolds or bubblers are welded, assembled, tested and packaged in the cleanroom.

For the most exacting requirements in cleanrooms, we rely on highly trained and experienced specialists. A high level of discipline and forward-thinking are among the demands we make of our employees. Regular retraining and further development in the area of cleanroom production ensures a high standard of quality for our products and thus your process reliability now and in the future.

Benefits of Cleanroom Manufacturing

- orbital welding of manifolds, UHP systems or complex vacuum systems
- assembly of components such as valves and bubblers
- quality checks and leak detection using helium leak testing
- residue-free cleaning
- particle-free packaging
- from production to packaging: everything takes place in a self-contained work process



THE BEST WELD SEAM IS NO WELD SEAM  
[Find out how that works here](#)



3D Bending

Fewer weld seams for more reliability and purity

With our 3D bending technology, we are in the position to reduce the number of welding seams to a requisite minimum. This is particularly advantageous in complex tube systems.

Along with our collaring expertise and our welding know-how, we produce space-saving and dead-space-optimized solutions for custom applications.

Benefits of 3D Bending Technology

- Minimization of weld seams for aspects of hygiene and safety
- CAD-construction and automatic production
- 3D measuring technology and documentation
- mid-process inspection for quality assurance



# “PRODUCTS FOR HIGH PURITY PROCESSES.”

Whether it's a standard product or a custom solution – everything is made to Dockweiler's high quality standard.”



## Tubes and Fittings

### Standard Dockweiler products

Our standard products satisfy the highest surface quality and purity standards. They are used in the semiconductor, pharmaceutical and chemical analysis industries, and further high tech industries, to transport fluids and gases. Our standard products include tubes, elbows, T-pieces, reducers and caps.



#### Technical Data

##### Dimensions

Imperial: 1/8" - 6"  
ISO: DN 8 - DN 200  
Metric: DN 4 - DN 150  
Pipe: DN/NPS 6 - DN/NPS 20

##### Materials

1.4404, 1.4435, UNS S31603 (316L), 1.4539, UNS N08367 (AL-6XN), UNS N08904 (904L), UNS N06022 (C22)

##### Surface

- $Ra \leq 0,80 \mu m - \leq 0,13 \mu m$
- bright finished, anodical cleaned, electropolished

##### Standards

ASME-BPE, DIN 11864, DIN 11865, DIN 11866

## COAX Tubes and Fittings

### The double-wall tube for critical media

With the COAX double-wall tube system we offer a safe solution for the safe transport of explosive, toxic, corrosive or highly viscous media. COAX consists of an internal process tube and an external safety tube, between which, for example, a control center is alerted to a carrier gas leakage or steam maintains fluidity of viscous media in the process tube.

FOR CRITICAL MEDIUMS: ►  
the COAX double-wall tube system



#### Technical Data

##### Dimensions

Imperial: 1/4" - 1"

##### Materials

1.4404, 1.4435, UNS S31603 (316L)

##### Surface

- $Ra \leq 0,80 \mu m - \leq 0,13 \mu m$
- bright finished, anodical cleaned, electropolished

## Presslok

### The alternative to welding

The Presslok system complements our product line. It allows for very quick, reliable and reproducible pipe connections for process cooling water, inert gases or low-pressure systems, without any welding.



#### Technical Data

##### Dimensions

Imperial: 1/2" - 4"

##### Materials

UNS S31603 (316L), UNS S30403 (304L)

##### Pressure Resistance

1/2" - 1 1/2": 20 bar and 2" - 4": 13 bar



Custom Fittings

**When standard do not meet the requirements**  
Customized fittings manufactured to your specifications are the tailor-made solution when standard fittings do not meet customer requirements. Our service starts with drafting and extends to 3.1 documentation. Custom components include:

- **T-pieces with excentric branch** for residue-free drainage
- **Branches with various angles**, e.g. 45° or 60°
- **flow-optimized Y-pieces**
- **180°-elbows with outlet**, called “Point-of-Use” elbows



Technical Data

<b>Dimensions</b>
Imperial, Pipe, ISO, Metric
<b>Materials</b>
1.4404, 1.4435, UNS S31603 (316L), 1.4539, UNS N08367 (AL-6XN), UNS N08904 (904L), UNS N06022 (C22)
<b>Surface</b>
• $Ra \leq 0,80 \mu m - \leq 0,13 \mu m$ • bright finished, anodical cleaned, electropolished
<b>Standards</b>
ASME-BPE, DIN 11864, DIN 11865, DIN 11866

All custom fittings are prepared with welding-optimized ends. At the end, they are appropriately cleaned and packaged. They are available in all current materials and in all Dockweiler surface qualities.

Connection Components

**Integrate instrumentation and control elements**  
Dockweiler connection components give you the option of integrating instrumentation and control elements to control temperature, flow rate and pressure in your system. These are manufactured for both gases and liquids, depending on the customer specification. Instrumentation T-pieces can be equipped with various sensors, which measure the flow rate while the system is in operation, for example.

In addition to threaded, flanged or clamp connections, the Dockweiler connection components can also be equipped with the patented ZeroCon connection. With our many years of manufacturing expertise, we ensure low dead space design and flow-optimized profile.

PURGE TEE  
for connecting measuring and control elements



Technical Data

<b>Dimensions</b>
Imperial, Pipe, ISO, Metric
<b>Materials</b>
1.4404, 1.4435, UNS S31603 (316L), 1.4539, UNS N08367 (AL-6XN), UNS N08904 (904L), UNS N06022 (C22)
<b>Surface</b>
• $Ra \leq 0,80 \mu m - \leq 0,13 \mu m$ • bright finished, anodical cleaned, electropolished

Connections

**For a wide range of applications**  
We offer an equally diverse range of stainless steel tube systems with corresponding connections and gaskets in Dockweiler quality. For the straight-forward connection of tubing components, our range includes aseptic screw connections, clamp or flange connections in accordance with DIN 11864 and TriClamp connections in accordance with DIN 32676. For the highest purity and impermeability standards, we offer our customers the patented ZeroCon connection and Dockweiler Cap.



Technical Data

<b>Dimensions</b>
Imperial: 1/4" - 1"
<b>Materials</b>
1.4404, 1.4435, UNS S31603 (316L), 1.4539, UNS N08367 (AL-6XN), UNS N08904 (904L), UNS N06022 (C22)
<b>Surface</b>
• $Ra \leq 0,80 \mu m - \leq 0,25 \mu m$ • bright finished, anodical cleaned, electropolished

Gaskets and O-Rings

**Total traceability**  
from production to assembly is already an industry standard for quality stainless steel components. In contrast, as a rule, traceability for elastomers ends with installation at the latest. Clear identification is no longer guaranteed.  
  
All Dockweiler gaskets are laser marked and satisfy USP Class VI and are made from FDA approved materials. This way, we are able to ensure total traceability, required in particular for pharmaceutical facilities.

Technical Data

<b>Dimensions</b>
Imperial: 1/4" to 6"
ISO: 13.50 mm - 114.30 mm
Metric: 6.00 mm - 154.00 mm
<b>Materials</b>
PTFE, FKM, PTFE/FKM, EPDM, VMQ, PTFE/316L, PTFE/EPDM



DOCKWEILER LASERMARKED GASKETS  
For total traceability





Flexible Hoses

PolyFlow – technical hoses

Dockweiler hoses made from high quality elastomer and thermoplastic produce flexible connections for system components. They have all necessary approvals (like FDA, USP, Class VI) and comply with the pharmaceutical requirements. For us, every hose is one of a kind: Lengths, connections and materials can be mixed and matched and are tailor made. TriClamp, aseptic connections, welding ends and ZeroCon are available as connectors. Dockweiler hoses are used in the chemical and pharmaceutical industries as well as the food sector and biotechnology sector. They are used wherever quick and flexible connections are required.



◀ DIVERSE CONNECTION OPTIONS:  
Dockweiler hoses with TriClamp, Aseptic connections, welding ends and ZeroCon

Technical Data

Measurements

Nominal Size: 1/4" - 2"  
Length: up to 40 m  
Temperature Range: from -60 °C to +180 °C

Material

Internal liner: EPDM, silicone, PTFE



Flextron – the “flexible” hose

The Dockweiler Flextron corrugated hose was developed for us in the semiconductor and fine chemical industries. The highest demands are placed on the purity of the process media in these industries. Flextron's electropolished inner surface allows for these requirements to be met in all aspects of the supply system - from the gas tank to the manufacturing facility.

Flextron is manufactured from mechanically corrugated stainless steel (1.4404), as standard. A stainless steel wire braid can also be used to achieve a higher pressure resistance. The unique combination of electropolished surface and flexible corrugated hose minimizes the risk of contamination and enables gas transport under full UHP conditions throughout the system. With Flextron, oscillations and vibrations can be decoupled and done to the highest purity standards.



Flextron with VCR connection

Flextron with ZeroCon connection

Flextron with optional wire braid and welding ends

Technical Data

Connection Sizes


1/4" - 1"

Material

1.4404, UNS S31603 (316L)

Surface

- Ra ≤ 0,40 µm / ≤ 0,25 µm
- electropolished



With its fittings, Dockweiler ensures highly reliable, hygienic and efficient control in the production process. Depending on the sector, application and the purity, cleanability and impermeability requirements, ball valves or T-valves are used.

Ball Valves and Valves

T-valves

are a combination of premium diaphragm valve and high quality stainless steel tubing. Here, to optimize dead space, a T-piece's outlet was orbitally welded with a valve body. Particular attention was paid to the combination of hygiene and costs in a pharmaceutical setting. The T-valve bridges the gap between standard diaphragm valves with a lot of dead space and very expensive block valves.



Ball valves

We categorize our ball valves into one-, two- and three-part versions. Ball valves are available with welding ends, VCR, cutting ring fittings or flange connections, depending on the size and area of application. For valves with cutting ring fittings, our VSR80 tube is the ideal combination.

Technical Data

Dimensions

Imperial, ISO, Metric

Materials

1.4435, 1.4404, UNS S31603 (316L), UNS N08367 (AL-6XN), UNS N08904 (904L), UNS N06022 (C22)

Surface

- Ra ≤ 0,80 µm - ≤ 0,25 µm
- bright finished, anodical cleaned, electropolished

Technical Data

Dimensions

Imperial, Metric

Materials

UNS 31603 (316L)/PTFE

Surface

- Ra ≤ 0,63 µm - ≤ 0,38 µm
- bright finished, electropolished



COMPLEX COMPONENTS FROM DOCKWEILER:  
Customized solutions suitable for your requirements ►



Customized Solutions

Custom production, single or small-scale production

When it comes to implementing complex components and systems, Dockweiler is your manufacturing specialist. Maximizing productivity is the primary goal.

This requires a highly reliable, efficient and hygienic solution. The focus here is on low dead space and surface optimization.

Whether it's a single or small-scale production run, contract production or customized manufacturing: Our team supports you with longstanding application knowledge and translates your requirements into suitable customized solutions. At Dockweiler, we always do our best when it comes to customer-specific solutions. We offer you an unparalleled synergy in manufacturing expertise.

Technical Data
<b>Dimensions</b> Imperial, ISO, Metric, Pipe
<b>Materials</b> 1.4404, 1.4435, 1.4539, 2.4602, UNS S31603 (316L), UNS N08367 (AL-6XN), UNS N08904 (904L), UNS N06022 (C22)
<b>Surface</b> <ul style="list-style-type: none"><li>• <math>Ra \leq 0,80 \mu m - \leq 0,13 \mu m</math></li><li>• bright finished, anodical cleaned, electropolished</li></ul>

Process Vessels

For safe transport and storage

Dockweiler process vessels comply with the highest standards for storage, transport and removal of critical or high purity mediums - for example, organometallic compounds in the fine chemistry or semiconductor industries. Our HPS series makes us the only manufacturer worldwide to offer these bubblers for solids, too.

From melt selection and the most meticulous orbital welding seams, to the perfect inner surface, our bubblers offer the high quality typical of Dockweiler, like an internal surface Ra value up to  $\leq 0,25 \mu m$  (10  $\mu in$ ) and are completely electropolished, down to the last welding seam.

Extensive testing of the whole bubbler protects the environment and people. All our process bubblers are helium-leak tested up to  $\leq 4.0 \times 10^{-9}$  mbar l s<sup>-1</sup>



Technical Data
<b>Materials</b> 1.4404, 1.4435, UNS S31603 (316L), UNS N08367 (AL-6XN), UNS N08904 (904L), UNS N06022 (C22)
<b>Application Areas</b> for fluids (HPL and ECO series) and solids (HPS)
<b>Volumes</b> from 200 ml to 56 l
<b>Surface</b> <ul style="list-style-type: none"><li>• <math>Ra \leq 0,80 \mu m - \leq 0,13 \mu m</math></li><li>• bright finished, anodical cleaned, electropolished</li></ul>



Welding Equipment

The innovative EcoPurge system

The EcoPurge System was developed to provide purge gas control and monitoring while orbital welding tube systems. Specifically the ID tool is designed to for use with either CFOS or EP tubing systems without affecting surface quality.

EcoPurge drastically reduces the volume of purge gas required for welding by creating a purge dam. While reducing consumption the tool also monitors O<sub>2</sub> concentrations and pressure in the weld zone. Together this allows for very quick, accurate, and colorless welding results. General reduction of 95% gas volume and up to 60% labor savings can be achieved.

Welding rings for stainless steel

Product safety plays a primary role in the production of pharmaceutical materials. In order to obtain the high quality as in the base material, unwanted microscopic metallographic constituents, which are created during the welding process, must be minimized. Dockweiler welding rings significantly reduce the formation of ferrite and thus ensure a value of less than 3%. Where raw materials have a high quota of molybdenum, any brittleness and the formation of corrosive components are reliably counteracted.



◀ IDEAL FOR THE SEMICONDUCTOR AND PHARMACEUTICAL INDUSTRIES:  
Specially developed for UHP and CFOS applications



# “ DOCKWEILER-SERVICE FROM A TO Z

Our expert knowledge for your processes: analyses, assessments, consulting, training and much more for your success. ”



## Laboratory Services

### Analyses, assessments and more

Quality is inextricably linked to our products and the manufacturing process. For example, a T-piece for the semiconductor industry is subjected to up to 50 different tests before it reaches the customer. Our Quality Department doesn't just put our own products through their paces. Dockweiler also offers a broad range of laboratory services for third parties.

Our services extend from positive material identification (PMI), x-ray inspections, cryotests, surface analyses, corrosion tests to pure gas analyses and helium leak testing. We are happy to carry out the tests required for your products in our own laboratory and advise you.



## Material Consultancy and Metallurgy

### Which stainless steel material is the right one?

Are you not sure which stainless steel material is the right one for your application? Would you like to know the difference between UNS S361603 and 1.4404?

Our metallurgists will help you out and will happily advise: on the right choice of materials and on technical questions such as weldability or resistance to corrosion. How does the sulfur content affect the welding seam or what properties does ferrite have? These are just a few of the common questions our experts are happy to answer.

## Cleaning Processes

### For various industrial applications

Different industries and areas of application have various requirements in the purity of surfaces. Thus Dockweiler offers a variety of different cleaning processes: from cleaning internal surfaces in accordance with ASTM A632, S3 and dry cleaning processes, up to the most up to date high purity ultra pure and vacuum cleaning process with subsequent residual gas analysis. Also available for highly complex geometries and capillary structures.

We supply the product purity you need for your process.



Engineering Services and Application Know-How

For technical custom solutions

We understand the specific challenges of diverse industries in the transport of high purity media. All our expertise flows together into our engineering know-how. In close contact with our customers we take ideas, rough sketches and develop them into tangible, technical, customized solutions. With regard to implementation, we apply the following: "If you can draw it, we can make it".

Take advantage of our engineering services with optimized manufacturing processes, customer-specific solutions and new developments. With decades of know-how in the pharmaceutical and semiconductor industries we are engineering partner to industry and research.

Technical Documentation

Material and test reports also online

Dockweiler is taking documentation quality to the next level with the WebCert digital certificate portal: All our certificates and test reports are available via this optional service. It means that our customers can view documents online as soon as the goods have left our warehouse.

This service is a big plus for plant operators in particular, since these days, material test reports are becoming increasingly more essential and extensive.



FIND OUT MORE:

You can find more information about WebCert here



Training

Dockweiler transfer know-How

We not only attach a great importance to training our employees, but we also offer our customers the opportunity to undergo training at Dockweiler on "stainless steel tube systems". In addition to regular webinars, we publish posts on YouTube for different topics.

We also provide interested installers, technicians and customers with the opportunity to study further directly in Neustadt-Glewe at one of our Dockweiler Academy events.



FIND OUT ONLINE:

Link to our YouTube Channel



Logistics and Warehouse Service

Quick availability for standard products

Availability is paramount to our customers. As a result, we maintain a stock of over 1500 km tubes and a million fittings and gaskets in our six international central storage facilities. These can be delivered within 24 hours, upon request.

So that you can operate in a more flexible way, alongside our classic consignment warehouses, Dockweiler also offers swap bodies and containers as mobile storage. The swap bodies can be used to carry out installation and pro-

duction projects (SKID manufacturing or system installations), for example.

Cleaning and packaging of the tubes and fittings is just as important so that these reach the customer safely and in a protected manner. We have been certified as an AEO(C) customs authorized economic operator since 2011 and as a recognized consignor since 2013. This guarantees quicker customs clearance and thus shorter delivery times.





Certificates



AD 2000 HPO



DIN EN ISO 9001



DIN EN ISO 14001



PED 2014/68/EU and AD 2000 WO



Additional certificates can be found on our website

[www.dockweiler.com](http://www.dockweiler.com)



Subsidiaries and Distribution Partners



<b>DOCKWEILER AG</b> <b>Headquarters</b> Neustadt-Glewe Germany Phone: +49 387 57 58 0 Email: info@dockweiler.com www.dockweiler.com	<b>Austria</b> <b>Dockweiler Austria GmbH</b> Ried/Innkreis Phone: +43 775 28 59 81 Email: office@dockweiler.at www.dockweiler.com	<b>Israel</b> <b>Dockweiler Middle East Ltd.</b> Givataim Phone: +972 3 571 5005 Email: sales@dockweiler-me.com www.dockweiler.com	<b>Slovenia</b> <b>Dockweiler d.o.o.</b> Trzin Phone: +386 1 564 23 22 Email: dockweiler@amis.net www.dockweiler.com	<b>France</b> <b>Tubes Technologies S.A.</b> Mions Phone: +33 478 20 37 38 Email: info@tubes-technologies.com www.tubes-technologies.com	<b>Switzerland</b> <b>Hans Kohler AG</b> Zürich Phone: +41 44 207 11 11 Email: mail@kohler.ch www.kohler.ch	<b>India</b> <b>Instrumentation &amp; Controls</b> Mumbai Phone: +91 22 24 93 41 25 Email: trivtech@vsnl.com
	<b>China</b> <b>Dockweiler China Co. Ltd.</b> Suzhou Phone: +86 136 5621 0301 Email: f.cheng@dockweiler.com www.dockweiler.com	<b>Japan</b> <b>Dockweiler Japan Ltd.</b> Chuo-ku, Tokyo Phone: +81 3 3277 0250 Email: sales@dockweiler.co.jp www.dockweiler.com	<b>Thailand</b> <b>Dockweiler Asia Co., Ltd.</b> Bangkok Phone: +66 32 709 662 Email: sales.asia@dockweiler.com www.dockweiler.com	<b>Greece</b> <b>Inox Style</b> Attica Phone: +30 210 55 95 918 Email: info@inoxstyle.gr www.inoxstyle.gr	<b>Turkey</b> <b>Durko Çevre Enerji Tekniği ve Ticaret A.Ş.</b> Istanbul Phone: +90 216 402 20 00 Email: info@durkocevre.com.tr www.durkocevre.com.tr	<b>Indonesia</b> <b>PT Cryogas</b> Tangerang Phone: +62 21 55 66 10 19 Email: rey@cryogas.com.my www.cryogas.com.my
	<b>Hungary</b> <b>Dockweiler</b> Siófok Phone: +36 209 71 51 91 Email: dockw.mo@gmail.com www.dockweiler.com	<b>Netherlands and Belgium</b> <b>Dockweiler B.V.</b> Zeewolde Phone: +31 36 845 01 21 Email: info@dockweiler.nl www.dockweiler.com	<b>United Kingdom</b> <b>Dockweiler UK Ltd.</b> Wrexham Phone: +44 19 78 66 03 30 Email: sales@dockweiler.co.uk.com www.dockweiler.com	<b>Canada</b> <b>Wika Instruments Ltd.</b> Oakville, Ontario Phone: +1 905 337 1611 Email: l.clarke@wika.ca www.wika.ca	<b>Ireland</b> <b>Aqua Process Solutions Ltd.</b> Hospital Phone: +353 61 38 36 71 Email: e.odonnell@apsl.ie www.apsl.ie	<b>Malaysia</b> <b>Flowquipt Technology Sdn Bhd</b> Puchong Selangor Phone: +60 12 36 31 134 Email: kcteh@flowquipt.com www.flowquipt.com
				<b>Cuba and Dominican Republic</b> <b>BDC International S.A.</b> La Habana Phone: +535 263 0957 Email: bdchav@hav.bdcint.cu www.bdcinternational.net	<b>Italy</b> <b>R.T.R. Roberto Tomassini Rappresentanze</b> Milano Phone: +39 02 433 192 21 Email: info@tomassinir.it www.tomassinir.it	<b>Singapore</b> <b>CSK-BIO Pte Ltd</b> Singapore Phone: +65 67 49 22 70 Email: sales@csk-bio.com www.csk-bio.com
				<b>USA</b> <b>Banner Industries, Inc.</b> Danvers, MA Phone: +1 978 777 0080 Email: newenglandsales@bannerindustries.com www.bannerindustries.com	<b>Norway</b> <b>Teknolab AS</b> Ski Phone: +47 66 81 34 70 Email: mail@teknolab.no www.teknolab.no	<b>Mega Valve &amp; Fitting Pte Ltd.</b> Singapore Phone: +65 67-561-191 Email: calvin.lim@megavalve.com.sg www.megavalve.com.sg
				<b>EUROPE</b>	<b>Poland</b> <b>Grupa JMC Sp. z o.o.</b> Warsaw Phone: +48 22 864 11 05 Email: grupajmc@grupajmc.pl www.grupajmc.pl	<b>South Korea</b> <b>Keytech Korea</b> Seoul Phone: +70 8871 1185 Email: keytechkorea@gmail.com www.keytechkorea.co.kr
				<b>Bulgaria</b> <b>Merkur Trading Ltd.</b> Sofia Phone: +35 929 92 23 46 Email: rraddev@merkur-trading.com www.merkur-trading.com	<b>Romania</b> <b>String Rumania</b> Buzau Phone: +40 238 72 62 80 Email: liviu.grigore@string.ro www.string.ro	<b>South Africa</b> <b>National Dairy Equipment (Pty) Ltd.</b> Cape Town Phone: +27 21 550 68 00 Email: info@nde.co.za www.nde.co.za
				<b>Croatia</b> <b>ASKON Internacional d.o.o.</b> Sveti Križ Začretje Phone: +385 49 228577 Email: info@askon.hr www.askon.hr	<b>Russia</b> <b>ABS Service</b> Moscow Phone: +7 495 744 10 40 Email: info@dockweiler.ru www.dockweiler.ru	<b>Tunisia</b> <b>Water Treatment Technologies</b> Sidi Daoud-La Marsa-Tunis Phone: +216 71 775 026 Email: wtt.tn@planet.tn www.wtt.tn
				<b>Czech Republic / Slovakia</b> <b>Bibus Metals</b> Brno Phone: +420 547 125 385 Email: vs@bibusmetals.cz www.bibusmetals.cz	<b>Serbia / Bosnia / Macedonia / Montenegro</b> <b>Eurocons group D.O.O</b> Vrsac Phone: +381 13 80 14 60 Email: goran@eurocons.rs www.eurocons.rs	<b>United Arab Emirates</b> <b>Super Technical FZCO</b> Dubai Phone: +971 488 618 00 Email: info@supertech.ae www.supertechanical.com
				<b>Denmark</b> <b>Alflow Scandinavia A/S</b> Vejen Phone: +45 76 96 21 30 Email: alflow@alflow.dk www.alflow.dk	<b>Spain</b> <b>Quilinox S.L.</b> Paterna (VALENCIA) Phone: +34 902 30 43 16 Email: quilinox@quilinox.com www.quilinox.com	<b>Woodmans Meditech LLC</b> Dubai Phone: +971 423 454 23 Email: woodmans@eim.ae www.woodmansllc.com
				<b>Finland</b> <b>Suomen Teknohaus Oy</b> Tuusula Phone: +358 927 47 21 0 Email: info@teknohaus.fi www.teknohaus.fi	<b>Sweden</b> <b>Calamo AB</b> Molkom Phone: +46 553 313 00 Email: sales@calamo.se www.calamo.se	<b>ASIA</b>
					<b>Greater China</b> <b>Leadinno Fluid System Technology</b> Shanghai Phone: +86 21 5515 7095 Email: sales@leadinno.com www.leadinno.com	<b>New Zealand</b> <b>Prochem Group (NZ) PTY Ltd</b> Hamilton Phone: +64 7 444 5458 Email: nzlsales@prochemgroup.co.nz www.prochem.com.au
					<b>First Elite Enterprise Co. Ltd.</b> Taiwan Phone: +886 2 87 97 88 99 Email: auto.pipe@msa.hinet.net www.autopipe.com.tw	



Your contact person

**Dockweiler AG**

An der Autobahn 10/20  
19306 Neustadt-Glewe  
Germany

Tel.: + 49 38757 58 0  
Fax: + 49 38757 58 222  
Email: [sales@dockweiler.com](mailto:sales@dockweiler.com)  
Internet: [www.dockweiler.com](http://www.dockweiler.com)

